

Garant GRIDLINE

CNC tool cabinet complete with drawers, 26×24G, Height mm / number of drawers: 1025/3**Order data**

Order number	970785 1025/3
GTIN	4062406163587
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Cabinet can be centrally locked by a cylinder lock. Cabinet can be centrally locked by a cylinder lock. With raised edge on 3 sides and **ribbed rubber mat. 100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawer **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Colour:

Body and drawer cabinet body RAL 7035 light grey, drawer fronts RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

For storage of tools, a drawer inlay No. 970705 is required.

Technical description

Weight	144 kg
Drawer usable area in G	26×24

Drawer usable depth	600 mm
Drawer usable width	650 mm
Usable height	900 mm
Drawer usable depth in G	24
Width	750 mm
Drawer usable width in G	26
Depth	700 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×24G
Type of product	CNC tool cabinet

Accessories

Drawer, 200 kg Drawer front height 300 mm	931165 300
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 1000 mm	931155 1000
Sheet metal cover top with raised edge on 3 sides Dimension in G 30X28	951970 30X28
Ribbed rubber mat Dimension in G 30X28	951975 30X28