

Garant GRIDLINE

**CNC tool cabinet complete with drawers, 26×24G, Height mm / number of drawers: 1025/4****Order data**

|              |               |
|--------------|---------------|
| Order number | 970785 1025/4 |
| GTIN         | 4062406163594 |
| Item class   | 9GK           |

**Description****Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Cabinet can be centrally locked by a cylinder lock. Cabinet can be centrally locked by a cylinder lock. With raised edge on 3 sides and **ribbed rubber mat. 100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawer **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

**Colour:**

Body and drawer cabinet body RAL 7035 light grey, drawer fronts RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

**For storage of tools, a drawer inlay No. 970705 is required.**

**Technical description**

|                     |        |
|---------------------|--------|
| Drawer usable width | 650 mm |
| Usable height       | 900 mm |

|  |  |
|--|--|
| Drawer usable depth                              | 600 mm   |
| Drawer usable area in G                          | 26×24  |
| Drawer usable width in G                         | 26   |
| Depth  | 700 mm   |
| Width  | 750 mm   |
| Drawer usable depth in G                         | 24   |
| Weight   | 125 kg   |
| Material thickness                               | 1.2 mm   |
| Drawer/pull-out shelf load capacity              | 200 kg   |
| Drawer runner extension (partial/full extension) | 100 %  |
| Drawer runner extension                          | Anti-tilt lock   |
| Height adjustment interval                       | 25 mm  |
| Cylinder lock                                    | modular lock barrel  |
| Colour selection                                 | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G          | 26×24G   |
| Type of product                                  | CNC tool cabinet   |

## Accessories

|   |              |
|---|--------------|
| Lock plate for GridLine Type HU21   | 914227 HU21  |
| Drawer,200 kg Drawer front height 300 mm                                  | 931165 300   |
| Drawer,200 kg Drawer front height 100 mm                                  | 931165 100   |
| Drawer,200 kg Drawer front height 200 mm                                  | 931165 200   |
| Tool cabinet casing for drawers Height 1000 mm                            | 931155 1000  |
| Sheet metal cover top with raised edge on 3 sides<br>Dimension in G 30X28 | 951970 30X28 |
| Ribbed rubber mat Dimension in G 30X28                                    | 951975 30X28 |