

Garant GRIDLINE

CNC auxiliary cabinet with drawers, 26×20G, Height mm / Type: 1025/4**Order data**

Order number	970755 1025/4
GTIN	4062406163563
Item class	9GK

Description**Version:**

Tool auxiliary cabinet in 60×28G, with drawers 26×20G. **With sliding doors**, centrally lockable by slide handle with cylinder lock, raised edge on 3-sides and **ribbed rubber mat. No anti-tilt device.** Drawers and pull-out shelves can be installed in both cabinet halves, without a centre partition. 100% full extension drawers with differential runners. Load capacity for drawers and pull-out shelves **200 kg**. Drawers with slots at 25 mm intervals to take slotted dividers.

Fitted with:

Number of drawers (No. 930635 size 75): 2

Number of pull-out shelves (No. 930656 size 75): 2

Colour:

Body, pull-out shelves and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

For storage of tools, a drawer inlay No. 970708 is required.

Technical description

Drawer usable width	650 mm
Width	1500 mm
Drawer usable depth	500 mm

Height	1025 mm
Weight	175 kg
Usable height	900 mm
Depth	700 mm
Drawer usable area in G	26×20
Drawer usable width in G	26
Drawer usable depth in G	20
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×20G
Type of product	CNC machine auxiliary cabinet

Accessories

Slide handle for GridLine Type HU12	914226 HU12
Drawer, 200 kg Drawer front height 75 mm	930635 75
Pull-out shelf 200 kg Installation height 75 mm	930656 75
Auxiliary cabinet with sliding doors with raised edge Height 1025 mm	932130 1025