

Garant GRIDLINE

**CNC cabinet complete with tool sockets, with roller shutter, for tool shanks:  
HSK40****Order data**

|              |               |
|--------------|---------------|
| Order number | 971309 HSK40  |
| GTIN         | 4062406164355 |
| Item class   | 9GI           |

**Description****Version:**

Equipped cabinet in 40×20G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

**Roller shutter of anodised aluminium profiles, colour not configurable.**

**Supplied with:**

Cabinet including mounting rails No. 971525 size 20 and shelves with tool sockets No. 971570.

**Colour:**

Body, mounting rails and shelves RAL 7035 light grey, **powder-coated.**

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

|  |  |
|--|--|
| Height                                 | 2000 mm  |
| Weight                                 | 146 kg   |
| Depth in G                             | 20   |
| Number of tool sockets                 | 198  |
| Depth                                  | 500 mm   |
| Width in G                             | 40   |
| Width                                  | 1000 mm  |
| Axial spacing A                        | 63 mm  |
| Number of tool block insert rails      | 9  |
| Mounting rails                         | 9 pair   |
| Material thickness                     | 0.9 mm   |
| Cabinet housing internal load capacity | 1000 kg  |
| Height adjustment interval             | 25 mm  |
| Cylinder lock                          | modular barrel   |
| Colour selection                       | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Cabinet fronts                         | Roller shutter   |
| Type of product                        | CNC cabinet  |

## Accessories

|   |              |
|---|--------------|
| Plastic insert Type HSK40   | 947390 HSK40 |
| Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20 | 971525 20    |
| Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks HSK40    | 971570 HSK40 |