

Garant GRIDLINE

## CNC cabinet complete with tool sockets, with roller shutter, for tool shanks: SK30



### Order data

Order number	971309 SK30
GTIN	4062406164058
Item class	9GI

### Description

#### Version:

Equipped cabinet in 40×20G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

**Roller shutter of anodised aluminium profiles, colour not configurable.**

#### Supplied with:

Cabinet including mounting rails No. 971525 size 20 and shelves with tool sockets No. 971570.

#### Colour:

Body, mounting rails and shelves RAL 7035 light grey, **powder-coated.**

#### Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Axial spacing A	72 mm
Width	1000 mm
Weight	146 kg
Number of tool sockets	180
Width in G	40
Depth	500 mm
Depth in G	20
Height	2000 mm
Mounting rails	9 pair
Number of tool block insert rails	9
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Cabinet fronts	Roller shutter
Type of product	CNC cabinet

## Accessories

Plastic insert Type SK30	947390 SK30
Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks SK30	971570 SK30
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20	971525 20