

Garant GRIDLINE

CNC large-capacity cabinet complete with tool sockets with plain sheet metal swing doors, for tool shanks: HSK40



Order data

| | |
|--------------|---------------|
| Order number | 971451 HSK40 |
| GTIN | 4062406164959 |
| Item class | 9GI |

Description

Version:

Equipped cabinet in 40×28G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

Supplied with:

Cabinet including mounting rails No. 971525 size 28 and shelves with tool sockets No. 971570.

Colour:

Body, mounting rails and shelves RAL 7035 light grey, doors RAL 7016 anthracite, **powder-coated.**

Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942573 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|--|--|
| Mounting rails | 2 pair |
| Depth | 700 mm |
| Usable height | 1845 mm |
| Number of tool block insert rails | 8 |
| Width in G | 40 |
| Width | 1000 mm |
| Weight | 115 kg |
| Depth in G | 28 |
| Height | 2000 mm |
| Number of tool sockets | 176 |
| Axial spacing A | 63 mm |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Cabinet fronts | Plain sheet metal swing door |
| Type of product | CNC large-capacity cabinet |

Accessories

| | |
|---|--------------|
| Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks HSK40 | 971570 HSK40 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 28 | 971525 28 |
| Plastic insert Type HSK40 | 947390 HSK40 |

Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm

940501 2000