

Garant GRIDLINE

## CNC large-capacity cabinet complete with tool sockets with plain sheet metal swing doors, for tool shanks: SK50



### Order data

Order number	971451 SK50
GTIN	4062406164874
Item class	9GI

### Description

#### Version:

Equipped cabinet in 40×28G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

#### Supplied with:

Cabinet including mounting rails No. 971525 size 28 and shelves with tool sockets No. 971570.

#### Colour:

Body, mounting rails and shelves RAL 7035 light grey, doors RAL 7016 anthracite, **powder-coated.**

#### Note:

For storage shelves and accessories for GridLine large-capacity cabinets see No. 942530 – 942573 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Number of tool sockets	48
Width	1000 mm
Depth	700 mm
Usable height	1845 mm
Depth in G	28
Axial spacing A	141 mm
Height	2000 mm
Number of tool block insert rails	8
Weight	115 kg
Width in G	40
Mounting rails	2 pair
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Cabinet fronts	Plain sheet metal swing door
Type of product	CNC large-capacity cabinet

## Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000
Plastic insert Type SK50	947390 SK50
Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks SK50	971570 SK50
Slide handle for GridLine Type GP11	914226 GP11

Mounting rails for shelves with tool sockets, pair suitable  
for cabinet depth in G 28

---

971525 28