

Garant GRIDLINE

Shelf with tool sockets for cabinet / compartment width 30 G, for tool shanks: HSK40



Order data

Order number	971560 HSK40
GTIN	4062406165277
Item class	9GI

Description

Suitable for:

Installation on mounting rails No. 971525.

Cabinet width / compartment width 30G (cabinets of width 60G consist of 2 compartments each 30G).

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Axial spacing A	63 mm
Depth	135 mm
Number of tool sockets	17
Height	54 mm
for tool shanks	HSK 40
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC carrier system

Accessories

Plastic insert Type HSK40	947390 HSK40
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 28	971525 28
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20	971525 20