

Garant GRIDLINE

## Shelf with tool sockets for cabinet / compartment width 40 G, for tool shanks: SK30



### Order data

Order number	971570 SK30
GTIN	4062406165321
Item class	9GI

### Description

#### Suitable for:

Installation on mounting rails No. 971525.

Cabinet width / compartment width 40G (cabinets of width 80G consist of 2 compartments each 40G).

#### Colour:

RAL 7035 light grey **powder coated**.

### Technical description

Depth	135 mm
for tool shanks	SK 30
Number of tool sockets	20
Height	54 mm
Axial spacing A	72 mm
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC carrier system

## Accessories

Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20

971525 20

Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 28

971525 28

Plastic insert Type SK30

947390 SK30