

Garant GRIDLINE

**Shelf with tool sockets for cabinet / compartment width 40 G, for tool shanks: C8****Order data**

Order number	971570 C8
GTIN	4062406165413
Item class	9GI

**Description****Suitable for:**

Installation on mounting rails No. 971525.

Cabinet width / compartment width 40G (cabinets of width 80G consist of 2 compartments each 40G).

**Colour:**

RAL 7035 light grey **powder coated**.

**Technical description**

Depth	135 mm
for tool shanks	C8
Number of tool sockets	8
Height	54 mm
Axial spacing A	104 mm
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC carrier system

## Accessories

Plastic insert Type C8	947390 C8
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 28	971525 28
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20	971525 20