

Garant GRIDLINE

**Upright cabinet, depth 28G, 2 base-supported pull-out frames, Height: 2000 mm****Order data**

Order number	971605 2000
GTIN	4062406165482
Item class	9GI

**Description****Version:**

Upright cabinet in 30×28G with base-supported pull-out frames. The 2-component Haptoprene® push handle can be locked with a cylinder lock. The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool stands, carrying rails, storage shelf trays, and perforated tool boards.

**Colour:**

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

**Note:**

2 carriers can be fitted next to each other within a 330 mm wide pull-out frame. Upright cabinets can be set up only on ground that is **absolutely level**.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 750 mm

Depth: 700 mm

Width in G: 30

Depth in G: 28

Pull-out frame drawers width: 330 mm

## Technical description

Vertical pull-out frame usable width	323 mm
Width	750 mm
Depth	700 mm
Weight	259 kg
Pull-out frame drawers width	330 mm
Vertical pull-out frame usable depth	627 mm
Height	2000 mm
Width in G	30
Depth in G	28
Vertical pull-out frame usable height	1750 mm
Material thickness	1.2 mm
Vertical pull-out frame load capacity	600 kg
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC heavy duty upright cabinet