

Garant GRIDLINE

Upright cabinet with base-supported pull-out frames fitted with tool sockets, for tool shanks: SK40



Order data

Order number	971655 SK40
GTIN	4062406165529
Item class	9GI

Description

Version:

Upright cabinet in 30×28G with base-supported pull-out frames. The 2-component Haptoprene® push handle can be locked with a cylinder lock. The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool stands, carrying rails, storage shelf trays, and perforated tool boards.

Colour:

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

Note:

2 carriers can be fitted next to each other within a 330 mm wide pull-out frame. Upright cabinets can be set up only on ground that is **absolutely level**.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 750 mm

Depth: 700 mm

Width in G: 30

Depth in G: 28

Pull-out frame drawers width: 160 mm

Technical description

Axial spacing A	85 mm
for tool shanks	SK 40
Number of tool sockets	312
Number of pull-out frames	4
Number of tool carriers No. 970130	24
Depth	700 mm
Width	750 mm
Width in units	36 E
Vertical pull-out frame usable height	1750 mm
Pull-out frame drawers width	160 mm
Weight	310 kg
Height	2000 mm
Width in G	30
Depth in G	28
Material thickness	1.2 mm
Vertical pull-out frame load capacity	600 kg
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC heavy duty upright cabinet

Accessories

Plastic insert Type SK40	947390 SK40
Tool carrier with tool sockets for tool shanks SK40	970130 SK40

