

Garant GRIDLINE

## Upright cabinet with base-supported pull-out frames fitted with tool sockets, for tool shanks: HSK100



### Order data

Order number	971655 HSK100
GTIN	4062406165659
Item class	9GI

### Description

#### Version:

Upright cabinet in 30×28G with base-supported pull-out frames. The 2-component Haptoprene® push handle can be locked with a cylinder lock. The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool stands, carrying rails, storage shelf trays, and perforated tool boards.

#### Colour:

Body RAL 7035 light grey, pull-out frames RAL 7016 anthracite **powder-coated**.

#### Note:

2 carriers can be fitted next to each other within a 330 mm wide pull-out frame. Upright cabinets can be set up only on ground that is **absolutely level**.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 750 mm

Depth: 700 mm

Width in G: 30

Depth in G: 28

Pull-out frame drawers width: 160 mm

## Technical description

Depth	700 mm
Width in units for tool shanks	36 E HSK 100
Vertical pull-out frame usable height	1750 mm
Width	750 mm
Number of tool sockets	120
Axial spacing A	127 mm
Weight	310 kg
Number of pull-out frames	4
Pull-out frame drawers width	160 mm
Height	2000 mm
Number of tool carriers No. 970130	24
Depth in G	28
Width in G	30
Material thickness	1.2 mm
Vertical pull-out frame load capacity	600 kg
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC heavy duty upright cabinet

## Accessories

Plastic insert Type HSK100	947390 HSK100
Tool carrier with tool sockets for tool shanks HSK100	970130 HSK100

