

**ROLLER****Anaconda WB chain clamp for pipes, Capacity for pipes up to: 6in****Order data**

Order number	868650 6
GTIN	4044942127612
Item class	84B

**Description****Version:**

Sturdy chain clamp for pipes for attaching to a workbench. For easy secure clamping of pipes using special serrated Vee-shaped clamping jaws and a sturdy clamping chain with a quick-release fastener.

- **Sturdy distortion-free cast design of the baseplate, with integral chain clamp vice, pipe support and bending machine.**
- **Specially serrated and hardened double vice jaws, easily exchanged, Vee-shaped for secure clamping of pipes.**
- **Clamping chain with sturdy chain links, easily clamped with quick-release fastener and trapezoidal thread spindle.**
- **For attachment to a workbench – please ensure compliance with the workbench load capacity.**

**Application:**

Secure clamping of pipes and solid materials, 1/8 inch – 6 inches (10 – 165 mm).

**Note:**

Adjustable material stand No. 919904 and workbenches from No. 921001 can be found in the Workstations and Storage catalogue.

**Technical description**

Jaw capacity	10 - 165 mm
Jaw capacity for pipes from – to	1/8 - 6 in
Weight	21 kg
Type of product	Pipe vice