

Garant GRIDLINE

ESD casing 16G with drawers, 12×20G, Casing height mm / number of drawers: 300/3mm**Order data**

Order number	972020 300/3
GTIN	4062406166496
Item class	9GG

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

Application:

Drawer casing for individual fitting to the ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 or for ESD workbenches No. 972150 – 972195.

Fitted with:

Drawer front height, mm: 50; 75; 100

Colour:

Body and drawers light grey similar to RAL7035, **ESD powder-coated**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive.

Technical description

Weight	31 kg
Drawer usable area in G	12×20

Drawer usable depth in G	20
Usable height	225 mm
Width	400 mm
Drawer usable width in G	12
Drawer usable width	300 mm
Drawer usable depth	500 mm
Usable height for drawers	225 mm
Number of drawers	3
Depth	650 mm
Height	300 mm
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	12x20G
Type of product	Workbench casing

Accessories

ESD drawer Drawer front height 75 mm	972035 75
ESD drawer Drawer front height 50 mm	972035 50
ESD drawer Drawer front height 100 mm	972035 100
ESD casing 16G for individual configuration with drawers Height of the housing 300 mm	972030 300
Lock plate for GridLine Type KO21	914227 KO21