

Garant GRIDLINE

**ESD casing 16G with drawers, 12×20G, Casing height mm / number of drawers: 500/4mm****Order data**

Order number	972020 500/4
GTIN	4062406166915
Item class	9GG

**Description****Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

**Application:**

Drawer casing for individual fitting to the ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 or for ESD workbenches No. 972150 – 972195.

**Fitted with:**

Drawer front height, mm: 50; 75; 100; 200

**Colour:**

Body and drawers light grey similar to RAL7035, **ESD powder-coated**

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive.

**Technical description**

Drawer usable area in G	12×20
Drawer usable depth in G	20

Weight	54 kg
Usable height for drawers	425 mm
Width	400 mm
Drawer usable depth	500 mm
Usable height	425 mm
Number of drawers	4
Depth	650 mm
Height	500 mm
Drawer usable width	300 mm
Drawer usable width in G	12
Material thickness	1 mm
Drawer/pull-out shelf load capacity	75 kg
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	12x20G
Type of product	Workbench casing

## Accessories

ESD drawer Drawer front height 100 mm	972035 100
ESD drawer Drawer front height 75 mm	972035 75
ESD drawer Drawer front height 50 mm	972035 50
ESD drawer Drawer front height 200 mm	972035 200
ESD casing 16G for individual configuration with drawerswheeled Height of the housing 500 mm	972032 500
Lock plate for GridLine Type KO21	914227 KO21