

Garant GRIDLINE

ESD worktop, Depth 750 mm, Worktop length: 1000mm**Order data**

Order number	972160 1000
GTIN	4062406166953
Item class	9GG

Description**Version:**

Support panel made of 50 mm **volume conductive** chipboard shelf. Surface coating made of **conductive** HPL plastic ESDS 0.8 mm. Underside with counter-balance made of white laminated plastic. All-round 3 mm **antistatic ABS edge band**.

Note:

Central hole for grounding plug No. 972827 size INT2W on the underside of the ESD worktop. Must be ordered separately.

The ESD worktop may only be used with ESD support legs and ESD stabilising plates.

Technical description

Grounding	centrally on the underside of the worktop
Worktop covering	HPL plastic, conductive
Material of worktop	Chipboard, volume conductive
Length	1000 mm
Colour of worktop surface	light grey RAL 7035
ESD security	yes
Thickness	51.6 mm
Coating thickness	0.8 mm
Worktop length	1000 mm
Volume conductive	yes
Cover coating, conductive	yes

electrostatic characteristic	EGB/ESD
Product name attribute	Depth 750 mm
Depth	750 mm
Type of product	Workbench top