

Garant GRIDLINE

ESD worktop, Depth 750 mm, Worktop length: 1500mm



Order data

Order number	972160 1500
GTIN	4062406166960
Item class	9GG

Description

Version:

Support panel made of 50 mm **volume conductive** chipboard shelf. Surface coating made of **conductive** HPL plastic ESDS 0.8 mm. Underside with counter-balance made of white laminated plastic. All-round 3 mm **antistatic ABS edge band. With internal steel tube as reinforcement profile**

Note:

Central hole for grounding plug No. 972827 size INT2W on the underside of the ESD worktop. Must be ordered separately.

The ESD worktop may only be used with ESD support legs and ESD stabilising plates.

Technical description

ESD security	yes
Volume conductive	yes
Thickness	51.6 mm
Reinforcement profile within the worktop	30×30×3 mm
Coating thickness	0.8 mm
Worktop covering	HPL plastic, conductive
Material of worktop	Chipboard, volume conductive
Length	1500 mm
Worktop length	1500 mm
Cover coating, conductive	yes
Colour of worktop surface	light grey RAL 7035

Grounding	centrally on the underside of the worktop
electrostatic characteristic	EGB/ESD
Product name attribute	Depth 750 mm
Depth	750 mm
Type of product	Workbench top