

Garant GRIDLINE

**ESD support leg incl. manual height adjustment, Number of pull-out frames:  
800 mm****Order data**

Order number	972185 800
GTIN	4062406167318
Item class	9GG

**Description****Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Height adjustment 150 mm.**

**Colour:**

Standard light grey paint finish similar to RAL 7035 **ESD powder-coated.**

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 972195 for stiffening. The height is to the underside of the worktop.

All plastic components are not ESD conductive. The support legs cannot be used for earthing.

electrical insulation: EGB/ESD

Height adjustment range: 800 - 950 mm

Width: 50 mm

Depth: 700 mm

suitable for worktop depth: 750 mm

**Technical description**

Width	50 mm
Depth	700 mm
suitable for worktop depth	750 mm
Height adjustment range	800 - 950 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
electrical insulation	EGB/ESD
Type of product	Support leg for height-adjustable workbench