

Garant GRIDLINE

**ESD materials supply trolley, Height: 1300mm****Order data**

Order number	972060 1300
GTIN	4062406167103
Item class	9GW

**Description****Version:**

**Frame and structure** made of rectangular steel hollow section with sheet metal base. Suspension slits on the front and back of the frame (at 50 mm intervals) for mounting storage shelves, rail with containers attached, etc. in size 1000 mm. **Threaded sockets** on the inside of the frame for fitting perforated panels. 4 TPE castors with parking brake, **Ø 125 mm** with grey abrasion-resistant **conductive wheels**.

**Application:**

Can be fitted with shelves, rail with containers and perforated panels in size 1000.

**Colour:**

Light grey similar to RAL 7035 **ESD powder-coated**.

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive.

**Technical description**

Weight	32 kg
Number of castors without parking brake	2
Height	1300 mm

Depth	700 mm
Width	1000 mm
Usable height	970 mm
Number of castors with parking brake	2
maximum load capacity	200 kg
Design version	Steel hollow section construction
Height adjustment interval	50 mm
electrostatic characteristic	EGB/ESD
Type of product	Materials supply trolley