

Garant GRIDLINE

**ESD materials supply trolley, Height: 1700mm****Order data**

Order number	972060 1700
GTIN	4062406167110
Item class	9GW

**Description****Version:**

**Frame and structure** made of rectangular steel hollow section with sheet metal base. Suspension slits on the front and back of the frame (at 50 mm intervals) for mounting storage shelves, rail with containers attached, etc. in size 1000 mm. **Threaded sockets** on the inside of the frame for fitting perforated panels. 4 TPE castors with parking brake, **Ø 125 mm** with grey abrasion-resistant **conductive wheels**.

**Application:**

Can be fitted with shelves, rail with containers and perforated panels in size 1000.

**Colour:**

Light grey similar to RAL 7035 **ESD powder-coated**.

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive.

**Technical description**

Depth	700 mm
Width	1000 mm
Number of castors without parking brake	2

Weight	35 kg
Height	1700 mm
Number of castors with parking brake	2
Usable height	1370 mm
maximum load capacity	200 kg
Design version	Steel hollow section construction
Height adjustment interval	50 mm
electrostatic characteristic	EGB/ESD
Type of product	Materials supply trolley