

Garant GRIDLINE

**eLevel+ workstation with ESD coating, Length: 1000mm****Order data**

Order number	972015 1000
GTIN	4062406167066
Item class	9GW

**Description****Version:**

**eLevel+ workstation, ESD conductive according to DIN EN 61340-5-1.** With continuous electrical adjustment for height. Height adjustment by pushbutton. Push-button adjustment for a suitable **worktop height. All-round 3 mm antistatic ABS edge band.** Central grounding point underneath the ESD worktop. The support legs are not used for earthing.

**Note:**

All plastic components (e.g. covering caps) are not ESD conductive.

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 972019 (crush hazard).**

**Technical description**

Height adjustment range (worktop surface) from – to	670 - 990 mm
Width	1000 mm
Weight	78 kg
Series	Workstation
Material of worktop	ESD worktop

Worktop thickness	40 mm
Control panel with display and memory functions	yes
Depth	800 mm
Stepless height adjustment	yes
Worktop covering	HPL plastic, conductive
Colour of worktop surface	light grey RAL 7035
Worktop length	1000 mm
Principle of height adjustment	only the worktop
Model	eLevel+
Worktop depth	700 mm
Coating thickness	0.8 mm
Plug type, input	F
Nominal voltage	250 V
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm
electrostatic characteristic	EGB/ESD
Type of product	Work table