

Garant GRIDLINE

ESD roller cabinet complete with drawers wheeled, 20×24G, Height mm / number of drawers: 885/5**Order data**

Order number	972425 885/5
GTIN	4062406166854
Item class	9GK

Description**Version:**

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Roller cabinet in 24×28G with 2 each ball-bearing **conductive** fixed wheels and castors, Ø 125 mm, castors with parking brakes. With raised edge on 4 sides. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). With **individual drawer release system** prevents the opening of drawers during transport.

Fitted with:

Drawer front height, mm: 75, 75, 100, 150, 200

Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**
- **Grounding via wheels.**

Technical description

Drawer usable depth in G	24
maximum load capacity	600 kg
Drawer usable width in G	20
with anti-roll lip	yes
Drawer usable width	500 mm
Weight	109 kg
Treadless tyres	yes
Electronic locking system can be retrofitted	yes
Drawer body usable height	600 mm
Drawer usable area in G	20×24
Drawer runner extension (partial/full extension)	100 %
Drawer usable depth	600 mm
Usable height	600 mm
Depth	700 mm
ComfortClose	no
Height	885 mm
Drawer/pull-out shelf load capacity	50 kg
Width	600 mm
Individual drawer release system	One-hand
Version	wheeled
Version	with drawers
Usable height for drawers	600 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	20×24G
Type of product	Assembly trolley

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------