

Garant GRIDLINE

ESD tool cabinet complete with drawers, 26×24G, Height mm / Model: 1000/6**Order data**

Order number	972440 1000/6
GTIN	4062406166878
Item class	9GK

Description**Version:**

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time. **Includes ESD grounding cable.**

Fitted with:

Drawer front height, mm: 50, 100, 100, 150, 200, 300

Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated.**

Note:

- **When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

Technical description

Weight	141 kg
Drawer usable width	650 mm

Height	1000 mm
Drawer usable width in G	26
Number of drawers	6
Drawer usable depth in G	24
Depth	700 mm
ESD security	yes
Drawer usable depth	600 mm
Width	750 mm
Usable height	900 mm
Drawer usable area in G	26×24
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
electrostatic characteristic	EGB/ESD
Product name attribute	26×24G
Type of product	Tool cabinet