

Garant GRIDLINE

ESD roller cabinet complete with drawers wheeled, 26×24G, Height mm / number of drawers: 985/7



Order data

Order number	972445 985/7
GTIN	4062406166908
Item class	9GK

Description

Version:

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Roller cabinet in 30×28G with 2 each ball-bearing **conductive** fixed wheels and castors, Ø 125 mm, castors with parking brakes. With raised edge on 4 sides. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

Complete with drawers 26×24G. 100% full extension drawers with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm). With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Fitted with:

Drawer front height, mm: 75, 75, 100, 100, 100, 100, 150

Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**
- **Grounding via wheels.**

Technical description

Data sheet

Treadless tyres	yes
with anti-roll lip	yes
ESD security	yes
Drawer runner extension (partial/full extension)	100 %
Drawer body usable height	700 mm
Drawer usable depth	600 mm
Individual drawer release system	One-hand
Number of drawers	7
Castor Ø	125 mm
maximum load capacity	600 kg
Electronic locking system can be retrofitted	yes
Drawer usable width in G	26
Drawer/pull-out shelf load capacity	50 kg
Drawer usable width	650 mm
Usable height	700 mm
Drawer usable depth in G	24
Width	750 mm
ComfortClose	no
Weight	140 kg
Fixed wheel Ø	125 mm
Drawer usable area in G	26×24
Height	985 mm
Depth	700 mm
Version	wheeled
Version	with drawers
Usable height for drawers	700 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular barrel

electrostatic characteristic	EGB/ESD
Product name attribute	26x24G
Type of product	Assembly trolley

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/972445-985/7>