

Garant GRIDLINE

ESD support columns, Height: 481 mm**Order data**

Order number	972080 481
GTIN	4062406167134
Item class	9GW

Description**Version:**

Made of sturdy sheet metal. Barrier-free working area, since no stabilising plate required. Insertion slots at 50 mm intervals on the front face, threaded sockets on the front and inner faces for holding other modules such as perforated panels, storage shelves etc. Support columns with side openings for cable routing. Supplied in pairs.

Suitable for:

ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 and ESD workbenches No. 972150 – 972160. Perforated sheet steel back panels 1 pc. No. 972100 or No. 972101.

Colour:

Light grey similar to RAL 7035 **ESD powder-coated.**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive. Support arm brackets cannot be mounted.

Technical description

Depth	100 mm
Series	Workstation

Weight	3 kg
maximum number of perforated panels	1 × No. 972100 or No. 972101
Width	40 mm
Material thickness	1 mm
Height adjustment interval	50 mm
electrostatic characteristic	EGB/ESD
Type of product	Support column