

Garant GRIDLINE

**ESD support columns, Height: 962mm****Order data**

Order number	972080 962
GTIN	4062406167141
Item class	9GW

**Description****Version:**

Made of sturdy sheet metal. Barrier-free working area, since no stabilising plate required. Insertion slots at 50 mm intervals on the front face, threaded sockets on the front and inner faces for holding other modules such as perforated panels, storage shelves etc. Support columns with side openings for cable routing. Supplied in pairs.

**Suitable for:**

ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 and ESD workbenches No. 972150 – 972160. Perforated sheet steel back panels 2 pc. No. 972100 or No. 972101.

**Colour:**

Light grey similar to RAL 7035 **ESD powder-coated.**

**Note:**

All plastic components (e.g. covering caps) and handles are not ESD conductive. Suitable for mounting support arm brackets.

**Technical description**

Width	40 mm
Weight	6 kg

maximum number of perforated panels	2 × No. 972100 or No. 972101
Series	Workstation
Depth	100 mm
Material thickness	1 mm
Height adjustment interval	50 mm
electrostatic characteristic	EGB/ESD
Type of product	Support column