

Garant GRIDLINE

ESD storage shelf of sheet metal, suitable for type: 1000**Order data**

Order number	972111 1000
GTIN	4062406167431
Item class	9GW

Description**Version:**

Made of sheet metal, with raised edge on 3 sides. Front face angled. Can be fitted with the edge facing upwards or downwards. **Depth adjustment range 110 mm.** Can be locked **horizontally at 90°** and **inclined at 110°.**

Suitable for:

Installation by **mounting** on ESD support columns No. 972080 and ESD materials supply trolley No. 972060 (only size 1000).

Colour:

Light grey similar to RAL 7035 **ESD powder-coated.**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive.

Technical description

Installation height	80 mm
Usable width	880 mm
Usable depth	300 mm
Depth adjustment range	110 mm
Storage shelf version	Standard
Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
electrostatic characteristic	EGB/ESD
Type of product	Storage shelf

