

Garant GRIDLINE

ESD casing 16G with drawers, 12×20G, Casing height mm / number of drawers: 400/4mm**Order data**

| | |
|--------------|---------------|
| Order number | 972020 400/4 |
| GTIN | 4062406180553 |
| Item class | 9GG |

Description**Version:**

Drawer cabinet with sturdy steel construction. **100% full extension drawers** with differential runners and 75 kg load capacity. Can be locked centrally with a cylinder lock.

Application:

Drawer casing for individual fitting to the ESD workstation No. 972010 – 972015, ESD height-adjustable workstations No. 972017 or for ESD workbenches No. 972150 – 972195.

Fitted with:

Drawer front height, mm: 75; 75; 75; 100

Colour:

Body and drawers light grey similar to RAL7035, **ESD powder-coated**

Note:

All plastic components (e.g. covering caps) and handles are not ESD conductive.

Technical description

| | |
|--------------------------|--------|
| Drawer usable depth in G | 20 |
| Drawer usable width | 300 mm |

| | |
|-------------------------------------|------------------|
| Drawer usable width in G | 12 |
| Width | 400 mm |
| Usable height | 325 mm |
| Drawer usable depth | 500 mm |
| Usable height for drawers | 325 mm |
| Height | 400 mm |
| Drawer usable area in G | 12×20 |
| Number of drawers | 4 |
| Weight | 40 kg |
| Depth | 650 mm |
| Material thickness | 1 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Cylinder lock | modular barrel |
| electrostatic characteristic | EGB/ESD |
| Product name attribute | 12×20G |
| Type of product | Workbench casing |

Accessories

| | |
|--|-------------|
| ESD drawer Drawer front height 100 mm | 972035 100 |
| ESD drawer Drawer front height 75 mm | 972035 75 |
| ESD casing 16G for individual configuration with drawers Height of the housing 400 mm | 972030 400 |
| Lock plate for GridLine Type KO21 | 914227 KO21 |