

ESD safe mat Width 91 cm, black, Length: 200cm**Order data**

Order number	972602 200
GTIN	662641699489
Item class	96C

Description**Version:**

Electrostatic dissipative safety mat with 14 mm thickness. Long-life laminated surface on a vinyl, micro-cell base which demonstrates an outstanding anti-fatiguing effect. Fitted with a 10 mm press stud and grounding cable. Good non-slip characteristics (R9 to DIN 51130 and BG rule BGR181) and easy twisting movement on the mat thanks to the teardrop pattern plate. Non-slip underlay prevents slipping, and four bevelled edges prevent tripping when walking onto the mat.

Standard:

Erfüllt **IEC 61340-4-1** (Kategorie DIF), gemessener Widerstand $R_g 10^6 - 10^9 \Omega$, $R_p 10^6 - 10^9 \Omega$.
Elektrostatische Aufladung (Geh-Test), erfüllt **ISO 6356** und **EN 1815**.

Supplied with:

Including earthing cable.

Technical description

Width	91 cm
Length	200 cm
Thickness	14 mm

Manufacturer's designation	Diamond Stat™
Standing in comfort	Anti-fatiguing
Standing in comfort	Anti-slip
Standing in comfort	Insulation (temperature)
Shock protection	Floor
Material characteristics	not oil-resistant
electrostatic characteristic	EGB/ESD
Product name attribute	black
Type of product	ESD floor mat