

Garant**ESD plug-in basic rack, Depth 400 mm, Height: 2000mm****Order data**

Order number	972500 2000
GTIN	4062406180744
Item class	911

Description**Version:**

Sturdy column frame of rectangular columns (50×25×1.25 mm) with slots at intervals of 40 mm for mounting cross beams / shelves. Column frames with non-conductive plastic end caps. No tools required for assembly. The high lateral stability eliminates the need for diagonal struts for stabilisation. Storage shelves are **ESD powder-coated**. A galvanised spring on the storage shelf ensure reliable contact with the installed earthing point.

With earthing pins welded on to the column frame. The conductivity of the earthing connection within the building must be checked by a qualified electrician.

Supplied with:

Includes ESD grounding cable.

Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **All plastic components (e.g. covering caps) are not ESD conductive.**

Technical description

Number of shelves	4
maximum bay load	900 kg
Assembled size basic rack width	1000 mm
Storage shelf clear width	900 mm
Shelf width	946 mm
Shelf load capacity / maximum distributed shelf load (on metal)	120 kg
Shelf thickness	38 mm
Height adjustment interval	40 mm
electrostatic characteristic	EGB/ESD
Product name attribute	Depth 400 mm
Type of product	Storage shelf