

Garant**GARANT Power Drill indexable drill Combination shank, 2xD, Ø DC: 15,5mm****Order data**

Order number	234000 15,5
GTIN	4045197739087
Item class	21S

Description**Version:**

The helical coolant ducts ensure very high stability, since they do not weaken the core of the drill.

Bore tolerance: -0.1 / +0.3 mm

Description:

For maximum performance and dimensional accuracy. Even for very difficult drilling situations up to 5xD.

Application:

With indexable inserts No. 234030 - 234098.

Use of the advertising text:

With inserts No. GG2340 - GG2389.

Suitable for:

Inserts SOGX 050204.

Note:

Other intermediate sizes in 1/10 increments available on request.

Technical description

Reach L_1	15.5 mm
Shank length L_s	50 mm
Shank $\varnothing D_s$	20 mm
Number of cutting edges Z	1
Pack of insert screws	239700 5IP (0.38 Nm)

ISO code indexable insert	SOGX 050204
Series	Power Drill
Nominal \varnothing D	15.5
Maximum adjustment limit V_{\max}	0.25 mm
Overhang L_A	48 mm
Indexable insert type for internal cutter	HB6535
Indexable insert type for internal cutter	HB6640
Indexable insert type for internal cutter	HB630
Indexable insert type for internal cutter	HB6810
Drill depth for indexable insert drill up to	2×D
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set 10 pieces Drive 5IP	239700 5IP
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 5IP	674252 5IP
Torque screwdriver, fixed setting set torque 0,38 N·m	211750 0,38