

**Garant**
**GARANT Power Drill indexable drill Combination shank, 2xD, Ø DC: 28,5mm**

**Order data**

Order number	234000 28,5
GTIN	4045197739841
Item class	21S

**Description**
**Version:**

The helical coolant ducts ensure very high stability, since they do not weaken the core of the drill.

**Bore tolerance:** -0.1 / +0.3 mm

**Description:**

For maximum performance and dimensional accuracy. Even for very difficult drilling situations up to 5xD.

**Application:**

With indexable inserts No. 234030 - 234098.

**Use of the advertising text:**

With inserts No. GG2340 - GG2389.

**Suitable for:**

Inserts SOGX 100408.

**Note:**

Other intermediate sizes in 1/10 increments available on request.

**Technical description**

Shank Ø D <sub>s</sub>	32 mm
Shank length L <sub>s</sub>	60 mm
Pack of insert screws	239700 10IP (2.8 Nm)
Number of cutting edges Z	1
Reach L <sub>1</sub>	58 mm

ISO code indexable insert	SOGX 100408
Series	Power Drill
Nominal $\varnothing$ D	28.5
for inch $\varnothing$	1 1/8 in
Maximum adjustment limit $V_{max}$	0.25 mm
Overhang $L_A$	81 mm
Indexable insert type for internal cutter	HB6535
Indexable insert type for internal cutter	HB6640
Indexable insert type for internal cutter	HB630
Indexable insert type for internal cutter	HB6810
Drill depth for indexable insert drill up to	2xD
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Torx Plus® insert screw set 10 pieces Drive 10IP	239700 10IP
Torque screwdriver, fixed setting set torque 2,8 N-m	211750 2,8