

Garant**GARANT Power Drill indexable drill Combination shank, 4×D, Ø DC m7: 26mm****Order data**

Order number	234010 26
GTIN	4045197740427
Item class	21S

Description**Version:**

The helical coolant ducts ensure very high stability, since they do not weaken the core of the drill.

Bore tolerance: $-0.1 / +0.35$ mm

Description:

For maximum performance and dimensional accuracy. Even for very difficult drilling situations up to 5×D.

Application:

With indexable inserts No. 234030 - 234098.

Use of the advertising text:

With inserts No. GG2340 - GG2389.

Suitable for:

Inserts SOGX 080407.

Note:

Other intermediate sizes in 1/10 increments available on request.

Technical description

Pack of insert screws	239700 8IP (1.3 Nm)
Reach L_1	104 mm
Shank length L_s	60 mm
ISO code indexable insert	SOGX 080407
Number of cutting edges Z	1
Shank Ø D_s	32 mm

Series	Power Drill
Nominal Ø D	26
Maximum adjustment limit V_{\max}	0.25 mm
Overhang L_A	125 mm
Indexable insert type for internal cutter	HB6535
Indexable insert type for internal cutter	HB6640
Indexable insert type for internal cutter	HB630
Indexable insert type for internal cutter	HB6810
Drill depth for indexable insert drill up to	4xD
Shank	ISO 9766
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3
Torx Plus® insert screw set 10 pieces Drive 8IP	239700 8IP