

HOLEX**Stepladder, single-sided access, Number of steps including platform: 4****Order data**

Order number	966500 4
GTIN	4045197741592
Item class	92L

Description**Version:**

Steps and stiles of aluminium with securely bolted step-stile connection, 4-way riveted aluminium ladder joint and 80 mm deep, serrated steps. Great stability due to tapered construction, non-slip end caps and large-area serrated standing platform. Ladder inclination 20°. Step spacing 235 mm.

Standard:

Gemäß DIN EN 131.

Technical description

Ladder length	1.54 m
Weight	5.8 kg
Cross beam height	50 mm
Accessibility	single-sided
Platform height	0.93 m
Working height approx.	3 m

outer width at bottom	0.49 m
Type of step	step
Length L	1.54 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder