

**HOLEX****Stepladder, single-sided access, Number of steps including platform: 5****Order data**

Order number	966500 5
GTIN	4045197741608
Item class	92L

**Description****Version:**

Steps and stiles of aluminium with securely bolted step-stile connection, 4-way riveted aluminium ladder joint and 80 mm deep, serrated steps. Great stability due to tapered construction, non-slip end caps and large-area serrated standing platform. Ladder inclination 20°. Step spacing 235 mm.

**Standard:**

**Gemäß DIN EN 131.**

**Technical description**

Ladder length	1.78 m
Weight	6.9 kg
Type of step	step
Working height approx.	3.25 m
Platform height	1.17 m
Accessibility	single-sided

outer width at bottom	0.52 m
Cross beam height	50 mm
Length L	1.78 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder