

HOLEX**Stepladder, single-sided access, Number of steps including platform: 6****Order data**

| | |
|--------------|---------------|
| Order number | 966500 6 |
| GTIN | 4045197741615 |
| Item class | 92L |

Description**Version:**

Steps and stiles of aluminium with securely bolted step-stile connection, 4-way riveted aluminium ladder joint and 80 mm deep, serrated steps. Great stability due to tapered construction, non-slip end caps and large-area serrated standing platform. Ladder inclination 20°. Step spacing 235 mm. With 2 high-strength Perlon straps.

Standard:

Gemäß DIN EN 131.

Technical description

| | |
|------------------------|--------------|
| Accessibility | single-sided |
| Weight | 8 kg |
| Ladder length | 2.01 m |
| outer width at bottom | 0.55 m |
| Cross beam height | 50 mm |
| Working height approx. | 3.5 m |

| | |
|-------------------------------------|------------|
| Type of step | step |
| Platform height | 1.4 m |
| Length L | 2.01 m |
| Ladders and platforms load capacity | 150 kg |
| Type of product | Stepladder |