

**Garant****Stepladder, single-sided access, Number of steps including platform: 5****Order data**

Order number	965900 5
GTIN	4045197742025
Item class	91B

**Description****Version:**

Treads and stiles of aluminium, permanent connection between treads and stiles, swaged in 4 ways. Great stability due to robust construction. With optimised ladder joint with a large contact face, 6-fold riveting and plastic protective cap.

80 mm deep treads with non-slip serrated surfaces.

EasyHandle Haptoprene® handle with clamping mechanism, non-slip BalanceBase end caps.

**Standard:**

Gemäß DIN EN 131-2, BetrSichV, TRBS 2121, DGUV Information 208-016 bzw. 208-017 und geltendem DGUV Regelwerk.

**Colour:**

Stiles anthracite RAL 7016 **powder-coated**.

Hoffmann perforated panel grid interval: 9×9

Length L: 1.98 m

Ladder length: 1.98 m

Working height approx.: 3.25 m

Platform height: 1.17 m

outer width at bottom: 0.53 m

Cross beam width: 73 mm

## Technical description

outer width at bottom	0.53 m
Working height approx.	3.25 m
Material	Aluminium
Cross beam width	73 mm
Platform height	1.17 m
Ladder length	1.98 m
Weight	7.5 kg
Accessibility	single-sided
Length L	1.98 m
Ladders and platforms load capacity	150 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Stepladder