

**Garant****Stepladder, single-sided access with GripStep, Number of steps including platform: 4****Order data**

Order number	965901 4
GTIN	4045197742049
Item class	91B

**Description****Version:**

Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Great stability due to robust construction.

With optimised ladder joint with a large contact face, 6-fold riveting and plastic protective cap. 80 mm deep treads with non-slip serrated surfaces.

EasyHandle Haptoprene® handle with clamping mechanism, non-slip BalanceBase end caps.

Supplied with **GripStep** step pad.

With plastic shelf.

**Standard:**

Gemäß DIN EN 131-2, BetrSichV, TRBS 2121, DGUV Information 208-016 bzw. 208-017 und geltendem DGUV Regelwerk.

**Colour:**

Stiles anthracite RAL 7016 **powder-coated**.

**Technical description**

Ladder length	1.73 m
---------------	--------

Material	Aluminium
Rung/step depth	80 mm
Working height approx.	3 m
Type of step	step
Accessibility	single-sided
outer width at bottom	0.5 m
Weight	6.6 kg
Cross beam height	73 mm
Platform height	0.93 m
Length L	1.73 m
Ladders and platforms load capacity	150 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Stepladder