

Garant**Stepladder, double-sided access, Number of steps: 2X5****Order data**

Order number	965920 2X5
GTIN	4045197742094
Item class	91B

Description**Version:**

Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Great stability due to robust construction.

80 mm deep treads with non-slip serrated surfaces.

EasyHandle Haptoprene® handle with clamping mechanism, non-slip BalanceBase end caps.

Solid aluminium ladder joint with 4 screw connections. With 2 high-strength Perlon straps to prevent splay. With SafeStep marking to identify the highest access step.

Without shelf.

Standard:

Gemäß DIN EN 131-2, BetrSichV, TRBS 2121, DGUV Information 208-016 bzw. 208-017 und geltendem DGUV Regelwerk.

Colour:

Stiles anthracite RAL 7016 **powder-coated.**

Technical description

Accessibility	double-sided
Working height approx.	2.75 m

Cross beam height	73 mm
Ladder length	1.16 m
outer width at bottom	0.49 m
Rung/step depth	80 mm
Type of step	step
Weight	8 kg
Length L	1.16 m
Ladders and platforms load capacity	150 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Stepladder