

Garant**Stepladder, single-sided access with GripStep, Number of steps including platform: 6****Order data**

Order number	965901 6
GTIN	4045197742063
Item class	91B

Description**Version:**

Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Great stability due to robust construction.
With optimised ladder joint with a large contact face, 6-fold riveting and plastic protective cap.
80 mm deep treads with non-slip serrated surfaces.
EasyHandle Haptoprene® handle with clamping mechanism, non-slip BalanceBase end caps.
Supplied with **GripStep** step pad.
With plastic shelf.

Standard:

Gemäß DIN EN 131-2, BetrSichV, TRBS 2121, DGUV Information 208-016 bzw. 208-017 und geltendem DGUV Regelwerk.

Colour:

Stiles anthracite RAL 7016 **powder-coated**.

Technical description

Working height approx.	3.5 m
------------------------	-------

Accessibility	single-sided
Platform height	1.4 m
Weight	8.5 kg
Rung/step depth	80 mm
Cross beam height	73 mm
Material	Aluminium
Type of step	step
outer width at bottom	0.55 m
Ladder length	2.23 m
Length L	2.23 m
Ladders and platforms load capacity	150 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Stepladder