

Garant**Stepladder, double-sided access, Number of steps: 2X3****Order data**

Order number	965920 2X3
GTIN	4045197742070
Item class	91B

Description**Version:**

Steps and stiles of aluminium, permanent connection between steps and stiles, swaged in 4 ways. Great stability due to robust construction.

80 mm deep treads with non-slip serrated surfaces.

EasyHandle Haptoprene® handle with clamping mechanism, non-slip BalanceBase end caps.

Solid aluminium ladder joint with 4 screw connections. With 2 high-strength Perlon straps to prevent splay. With SafeStep marking to identify the highest access step.

Without shelf.

Standard:

Gemäß DIN EN 131-2, BetrSichV, TRBS 2121, DGUV Information 208-016 bzw. 208-017 und geltendem DGUV Regelwerk.

Colour:

Stiles anthracite RAL 7016 **powder-coated**.

Technical description

outer width at bottom	0.44 m
Ladder length	0.69 m

Type of step	step
Accessibility	double-sided
Weight	5.4 kg
Working height approx.	2.25 m
Rung/step depth	80 mm
Cross beam height	73 mm
Length L	0.69 m
Ladders and platforms load capacity	150 kg
Hoffmann perforated panel grid interval	9×9
Type of product	Stepladder