

**Garant****Air Cleaning Point, Type: S****Order data**

Order number	986000 S
GTIN	2050001786005
Item class	96U

**Description****Version:**

Sturdy and robust cabinet of sheet steel with pneumatically driven extraction system and collection container. Operation of the extraction is performed by a foot pedal at the front. With castors and push handle at the rear for ease of transport.

All you need for operation is a compressed-air connection in the workshop.

**Application:**

For easy and thorough cleaning of workpieces and tools, using compressed air. Dust, chips, oils and liquids are extracted and deposited in the collection container.

**Supplied with:**

With GARANT compressed air gun No. 080123 size AIR, hose and Easyfix compressed air gun holder No. 955750 size 1, Easyfix plastic box No. 955790 size 74.

**Colour:**

RAL 7016 anthracite.

**Note:**

Spare filter mat can be found under No. 986001 at [www.hoffmann-group.com](http://www.hoffmann-group.com)

**Technical description**

Depth	450 mm
Width	570 mm
Type	S
Height	1300 mm
Weight	50 kg
Compressed air connection	DN 7.2
Working height	870 mm
Drip catch volume	20 l
Type of product	Cleaning station

---

## Accessories

Spare filter mat for Air Cleaning Point Type 1	986001 1
--	----------