



## LED headlamp with rechargeable battery, Type: I-VIEW



### Order data

Order number	081487 I-VIEW
GTIN	5708997350263
Item class	08C

### Description

#### Version:

Innovative LED work headlamp with wide spread of light for **optimum illumination of the entire work area**. Light-weight slim profile lamp. **Non-contact switching on and off, thanks to sensor system with two lighting levels.**

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

USB charger.

IP Index of Protection: IP 65

Manufacturer's designation: I-VIEW

ATEX zone: no

Illumination: 125 - 250 lm

Working life: 3 - 6 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

### Technical description

Including belt pocket	no
IP Index of Protection	IP 65
Manufacturer's designation	I-VIEW
Illumination	125 - 250 lm
Battery capacity	1.6 Ah

Battery voltage	3.8 V
Power supply	12
Working life	3 - 6 h
Weight	240 g
ATEX zone	no
Number of rechargeable batteries contained	1
Overall length	105 mm
Overall height	43 mm
Overall width	52 mm
Type of rechargeable battery	Lithium-ion
Type of product	Headlamp