

3M Scotch-Brite™

Abrasive fleece pad CF-PRO, 152×228 mm, Fleece structure: 1000



Order data

Order number	555999 1000
GTIN	4064035074135
Item class	53M

Description

Version:

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. High-performance fleece with **extremely dense grit distribution** deep into the fibres of the material. The special type of fleece structure permits **aggressive grinding characteristics**, a very long working life without clogging and an even **more uniform finish**.

Advantage:

- **Adapts to the shape of the component.**
- **The open structure prevents clogging and reduces heat development.**
- **Consistent reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander. **Fine / very fine:** for cleaning delicate surfaces, for removing light scratches on metals. Also suitable for applying fine / very fine matt finishes to steels and non-ferrous metals.

Technical description

Grit equivalent	600 - 1000
3M designation	CF-PRO
Version	S Ultra Fine
Grit designation	very fine
Fleece structure	1000

Colour	grey
Iron, sulphur and chlorine constituents	< 0.1 %
Width	152 mm
Length	228 mm
Product name attribute	152×228 mm
Type of product	Abrasive fleece pad

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		

Accessories

Hand block	556020
Mandrel	556030