

**PNMG 1106XNEN-GH, PR1510, Type: GG****Order data**

Order number	223314 GG
GTIN	4960664732876
Item class	25A

Description**Version:**

10-edge pentagonal indexable inserts for stable and economical machining.

GH - stable cutting edge.

Note:

Standard application values for $a_e = 0.3 \times D$.

Plane edge: 2 mm

Feed f_z per tooth: 0.3 mm

Technical description

Type	GG
Feed f_z per tooth	0.3 mm
Number of changes/inserts	10
ISO code indexable insert	PNMG 1106XNEN-GH
Grade	PR1510
Tool material	Carbide

Plane edge	2 mm
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	180 m/min	K
dry	suitable		
Air	suitable		