


**PNEG 1106XNER-W Wiper, PR1510, Type: GG**

**Order data**

Order number	223326 GG
GTIN	4960664732890
Item class	25A

**Description**
**Version:**

10-edge pentagonal indexable inserts for stable and economical machining.  
W - 2-edge wiper insert.

**Note:**

Standard application values for  $a_e = 0.3 \times D$ .

Plane edge: 10 mm

Feed  $f_z$  per tooth: max. 0.2 mm

**Technical description**

Type	GG
Feed $f_z$ per tooth	max. 0.2 mm
Number of changes/inserts	10
ISO code indexable insert	PNEG 1106XNER-W
Grade	PR1510
Tool material	Carbide

Plane edge	10 mm
Type of product	Indexable insert for milling

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
GG(G)	suitable	180 m/min	K
dry	suitable		
Air	suitable		