

**Mitutoyo**
**Digital display, Number of displayed axes: 2**

**Order data**

Order number	499356 2
GTIN	4946368693538
Item class	44D

**Description**
**Version:**

Easy-to-operate display unit for connection to linear measurement systems. Display range: 8 digits and sign (–), mains connection: 220 Volt.

**Function:**

Zero setting, changing the counting direction, mm / inch changeover. Halving the displayed value, ABS / INC coordinate switching, addition / subtraction, pitch circle calculation, programmable. **Comprehensive calculation functions:** (+, –, ×, ÷, COS, SIN, TAN, ARC,  $\sqrt{\quad}$ ,  $\pi$ ), function buttons for milling machines and lathes, hole sequence machining.

**Supplied with:**

Mains cable (2 m) and spare fuse.

**Optional extras:**

Interface unit (RS 232, USB, Digimatic input) for recording the tool offset, linear measuring scale No. 499240 / 499241.

**Technical description**

Scale divisions	0.0001 / 0.0005 in
Scale divisions	0.005 / 0.001 mm
Width	80 mm
Length	260 mm

Height	167 mm
Power supply	Mains operated
Reversible reading	mm / Inch
Type of product	Digital display