



Side lock arbor Form AD, BT 30 short, Clamping range \varnothing D1: 20mm



Order data

Order number	302595 20
GTIN	4250122697985
Item class	36E

Description

Version:

All shanks burnished.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Overhang dimension A: 63 mm

External \varnothing D: 52 mm

Spare clamping screw No. 30 9900: 20

Technical description

Overhang dimension A	63 mm
External \varnothing D	52 mm
Spare clamping screw No. 30 9900	20
Clamping \varnothing D ₁	20 mm
Adapter	BT 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud 45° sealed suitable for steep tapers 30	308765 30
Pull stud 60° sealed suitable for steep tapers 30	308785 30
Pull-stud 60° sealed suitable for steep tapers 30	308780 30
Pull stud 45° sealed suitable for steep tapers 30	308760 30
Spare clamping screw for chucks with clamping Ø D1 20 mm	309900 20