

**Side lock arbor Form AD, BT 30 short, Clamping range Ø D1: 18mm****Order data**

Order number	302595 18
GTIN	4250122697978
Item class	36E

Description**Version:**

All shanks burnished.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	16
External Ø D	50 mm
Overhang dimension A	63 mm
Clamping Ø D ₁	18 mm
Adapter	BT 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm

Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/302595-18>